DISTRIBUTED BY:



ST. 1916

INDSUPPLY.COM 800-288-3838





Cleanroom Wipes

Personal Protection

Cleanroom Liquid Cleaners

Cleanroom Paper

Cleanroom Tacky Mats

Sterilization Pouches

Cleanroom Absorbent Mat

Surface Cleaning Tools



Products Specially Developed to for Cleanrooms



What is a cleanroom?

A cleanroom is a controlled environment where airborne particulate matter such as dust, microbes, and aerosol particles are filtered out to provide a certain level of cleanliness. This control is achieved by air pressure and filters. Positive pressure keeps new particles from entering the clean area. The fewer the particles, the cleaner the room is. In order to prevent particles from getting into the environment, everything that enters the environment needs to be cleaned or covered.

Cleanroom Classifications

Generally cleanrooms are classified by how many particles are found in a cubic foot of space. ISO defines nine different cleanroom classifications, ranging from ISO 1 to ISO 9. The most common cleanrooms fall somewhere in the ISO 5 to ISO 8 range. ISO 4 at any given time has 352 particles in a cubic foot of air and an ISO 8 cleanroom has 3.5 million. A typical room has 35 million particles circulating in the air.

ISO 5 (Class 100) Cleanroom

Walls, floors, and ceilings should be non-porous/smooth and absolutely no linting fabric is permitted. Personnel would typically be wearing beard covers, face masks, shoe covers, gloves, hair nets, and coveralls. Gloves used in these environments should be removed from the cardboard box before they are brought in the cleanroom. Gowning is performed outside of the cleanroom. Polyester sealed-edge cleanroom wipes are commonly used in these environments. Certain poly-cellulose and polypropylene cleanroom wipes can also be used in some circumstances.

ISO 6 (Class 1,000) Cleanroom

Walls, floors, and ceilings should be non-porous/smooth and absolutely no linting fabric is permitted. Personnel would typically be wearing beard covers, shoe covers, hair nets, and coveralls. Poly-cellulose, polypropylene, polyester, and cotton cleanroom wipes can be used in these environments.

ISO 7 (Class 10,000) Cleanroom

Walls, floors, and ceilings should be non-porous/smooth and absolutely no linting fabric is permitted. Personnel would typically be wearing beard covers, hair nets or bouffant caps, and lab coats. Shoe covers might also be worn in some environments. Poly-cellulose, polypropylene, polyester, and cotton cleanroom wipes can be used in these environments.

ISO 8 (Class 100,000) Cleanroom

Walls and floors should be non-porous/smooth, and no carpeting or fabric cushioned chairs should be used. Personnel would typically be wearing beard covers, hair nets or bouffant caps, and lab coats. Poly-cellulose, polypropylene, polyester, and cotton cleanroom wipes can be used in these environments.

Cleanroom Classifications*							
Class	FED STD 209E	Maximum concentr	Maximum concentration limits (particles/m³ of air for particles equal to and larger than the sizes listed below.				
Class	Equivalent						
ISO 1		10	2				
ISO 2		100	24	10	4		
ISO 3	1	1,000	237	102	35	8	
ISO 4	10	10,000	2,370	1,020	352	83	
ISO 5	100	100,000	23,700	10,200	3,520	832	29
ISO 6	1,000	1,000,000	237,000	102,000	35,200	8,320	293
ISO 7	10,000				352,000	83,200	2,930
ISO 8	100,000				3,520,000	832,000	29,300
ISO 9					35,200,000	8,320,000	293,000



Our best selling Controlled Environment Solutions are marked with this symbol.

Types and Benefits of Wipe Materials

Polyester

Polyester material yields exceptional durability and cleanliness. Edges can be thermally sealed to prevent loose ends and linting. Additional measures can be taken to further enhance cleanliness such as washing and processing / packaging the wipe in a cleanroom. Polyester wipes with sealed edges are commonly used in ISO 3-4 (Class 1-10) Cleanrooms, Polyester wipes without sealed edges can be used in ISO 5-6 (Class 100-1,000) Cleanrooms.

Polyester/Cellulose Blends

These wipes can be engineered to meet unique requirements. Polyester/Cellulose blends are clean, absorbent, and an economic choice. Like polyester wipes, this material can be cleanroom processed to enhance cleanliness. They are common in ISO 5-8 (Class 100-100,000) Cleanrooms.

Polypropylene

Polypropylene is soft, non-abrasive, and solvent resistant. It's suitable for wiping sensitive surfaces and components. Polypropylene can be cleanroom processed and washed to further enhance cleanliness. It can be presaturated with a variety of solvents, sterilized, and cut to any size. Common for ISO 6 (Class 1000), in some cases ISO 5 (Class 100) Cleanrooms.

Minimum Wipe Recommendations*						
	ISO 8 (Class 100,000)	ISO 7 (Class 10,000)	ISO 6 (Class 1,000)	ISO 5 (Class 100)	ISO 4 (Class 10)	
Nonwoven Poly-Cellulose	•	•	•	•		
Polypropylene	•	•	•	•		
Polyester Knit			•	•		
Polyester, Sealed Edges					•	

^{*}These diagrams are a recommendation only. Follow your specific cleanroom or company procedural manual before this guide. The information supplied is for guidance only and should not be construed as a warranty. All implied warranties are expressly disclaimed, including without limitation any warranty of merchantability and fitness for use. All users of the material are responsible for assuring that it is suitable for their needs, environment and end use. All data is subject to change as deemed appropriate.

Cleanroom Wipes

Dry Cleanroom Wipes

- Our cleanroom wipes are made from the lowest-linting substrates including nonwoven poly-cellulose and polyester
- They are manufactured with materials that are free of bonding agents, adhesives or chemical additives
- With options for ISO Class 3 (Cleanroom Class 10) to ISO Class 7+ (Cleanroom Class 10,000), there is a wipe for virtually any cleanroom environment.



Additional sizes for Cleanroom Wipes are available



Dry Non-Sterile Wipes

NOVA-TECH® Wipes (ISO Class 5-6)							
s/cs							
/cs							
/cs							
tut Edges							
/cs							
/cs							
ULTIMATE 70® Wipes (ISO Class 3-4)							
ed Edges							
/cs							

Dry Sterile Wipes

Item	Packaging	Size	Selling Unit			
COBALT BLUE® Wipes (ISO Class 5-6)						
Validated Sterile	Nonwoven Cleanr	room Wipes				
NT1-99CB	Bag	9" x 9"	25 wipes/bg, 6 bgs/master bg - 10 master bgs/cs			
NT1-1212CB	Bag	12" x 12"	20 wipes/bg, 6 bgs/master bg - 7 master bgs/cs			

3

P: 800.942.9199 F: 216.279.0019 hospecobrands.com Controlled Environment Solutions

GRAB-EEZ° Cleanroom Wipes and Dispenser

- · New stainless steel construction
- · Redesigned cover makes loading wipes easier
- · Optional plastic shield protects wipes inside
- Unique double C-fold wipes dispense one-at-a-time to eliminate contamination and waste
- ISO Class 5 (Class 100) Cleanroom Compatible
- Eliminates wasteful wipe usage and crosscontamination



Item	Description	Size	Selling Unit
GE-NT1-99	Nonwoven Poly/Cellulose Cleanroom Wipes - Made in USA	9" x 9"	150 wipes/bg - 12 bgs/cs
GE-DISP-SS	Cleanroom Wipe Dispenser, Stainless Steel – suitable for use in ISO Class 5 (Class 100) cleanrooms	-	1 each



- · Reduce the use of squirt bottles and dipping cans
- · Reduce the amount of isopropyl alcohol used
- Use the exact percentage of IPA each application
- More even distribution of alcohol on the wipe and hence the wiping process
- Fewer VOCs (Volatile Organic Compounds)
- Safer to use, ship, and store than flammable liquids
- Convenience: No pouring, spraying, filtering, or diluting



A 70% concentration of ethanol or isopropyl alcohol has been demonstrated to be the most effective. Water acts as a catalyst and plays a key role in denaturing the proteins of vegetative cell membranes. The water content slows evaporation, therefore increasing surface contact time and enhancing effectiveness.

https://ehs.umich.edu/wp-content/uploads/2020/05/70-alcohol-FAOs.pdf

Pre-saturated Non-Sterile Wipes

PVC Plastic Tub

Item	Packaging	Size	Selling Unit				
FREE-SAT™ Wipes (ISO Class 5+)							
(70% IPA/30%	DI Water) Polyester	⁄Cellulose, Ab	sorbent & Non-Shedding				
FS-NT1-77 ★	PVC Plastic Tub	7" x 7"	100 wipes/tub - 12 tubs/cs				
FS-NT1-69-9C	Canister	6" x 9"	100 wipes/roll, 9 canisters/case				
FS-NT1-99	Bag	9" x 9"	75 wipes/bg - 12 bgs/cs				
(70% IPA/30%	DI Water) Polypropy	lene, Non-Ab	rasive & Solvent Resistant				
FS-NTP-911	Bag	9" x 11"	50 wipes/bg - 24 bgs/cs				
(85% IPA/15%	DI Water) Polypropy	lene Non-Abi	rasive & Solvent Resistant				
FS-NTP-1711.85	Bag	17" x 11"	50 wipes/bg - 20 bgs/cs				
SELECT-SAT® Wipes (ISO Class 5+) - Create Your Own Pre-saturated Non-Sterile Wipes							



Pre-saturated Sterile Wipes

Item	Description	Size	Selling Unit
COLBALT BLUE® W	/ipes (ISO Class 5+)		
FS-NTP-911.35CB	Sterile Polypropylene Wipes Saturated With 70% IPA / 30% Di Water In Resealable Bags, Non-Abrasive & Solvent Resistant	9"x 11"	35 wipes/bg - 20 bgs/cs
FS-NT1-912.35CB	Sterile Non-Woven Polyester Wipes Saturated With 70% IPA / 30% Di Water in Resealable Bags	9"x 12"	35 wipes/bg - 20 bgs/cs

Personal Protection

Bee-Safe® Bouffant Caps

- Polypropylene nonwoven construction
- Soft and comfortable
- · Breathable for long periods of wear
- · Elastic band for secure fit



Item #	Size	Color	Selling Unit
GAH-BP-21-WH	21"	White	100/bg - 10 bgs/cs
GAH-BP-21-BL	21"	Blue	100/bg - 10 bgs/cs
GAH-BP-24-WH ★	24"	White	100/bg - 10 bgs/cs
GAH-BP-24-BL ★	24"	Blue	100/bg - 10 bgs/cs
GAH-BP-28-WH	28"	White	100/bg - 10 bgs/cs
GAH-BP-28-BL	28"	Blue	100/bg - 10 bgs/cs

Bee-Safe® Beard Covers

- Polypropylene nonwoven construction
- Soft and comfortable
- Non-linting
- · Elastic band for secure fit and closure
- Lightweight



Item #	Size	Color	Selling Unit
GAH-BRD-WH	18"	White	100/bg - 10 bgs/cs

Bee-Safe® Polypropylene Hood

- Provides complete head coverage
- Made of lightweight, low-linting and breathable polypropylene material
- Latex-free



Item#	Size	Color	Selling Unit
GAH-HOOD-WH	One Size	White	100/bg - 10 bgs/cs
GAH-HOOD-BL	One Size	Blue	100/bg - 10 bgs/cs

SS-NT1-77

Dry Nonwoven Cleanroom Wipes - Ready for Custom Saturation, Absorbent & Non-Shedding

100 wipes/tub - 12 tubs/cs

Bee-Safe® Shoe Covers

Polypropylene Shoe Cover Features

- Low-linting nonwoven fabric helps filter particulates for contamination control
- Non-skid base features a wide traction pattern for enhanced grip
- Elastic band gives secure yet comfortable fit around the shoes

Super Sticky Polyethylene Coated Shoe Cover Features

- · Super sticky base to reduce slipping and sliding
- · Light liquid splash protection / water resistance
- · Latex-free elastic edges to minimize allergic reactions; seamless



Item #	Size	Color	Selling Unit				
Polypropylene Shoe Covers - 40 GSM							
GAH-SP-NS-LG	Large	Blue	100/bg - 3 bgs/cs				
GAH-SP-NS-XL	X-Large	Blue	100/bg - 3 bgs/cs				
GAH-SP-NS-2XL	2-XL	Blue	100/bg - 3 bgs/cs				
Super Sticky Polyethylene	Coated Shoe Covers						
GAH-SC-S-LG	Large	White	100/bg - 3 bgs/cs				
GAH-SC-S-XL	X-Large	White	100/bg - 3 bgs/cs				

Pharma-Coat® **Disposable Lab Coat**

- · Non-shedding
- Spunbond polypropylene
- Elastic wrists
- No Pockets
- ISO Class 7-8



Item #	Size	Color	Selling Unit
PCOAT797-S	S	White	10/bg - 3 bgs/cs
PCOAT797-M	M	White	10/bg - 3 bgs/cs
PCOAT797-L	L	White	10/bg - 3 bgs/cs
PCOAT797-XL	XL	White	10/bg - 3 bgs/cs
PCOAT797-2XL	2XL	White	10/bg - 3 bgs/cs
PCOAT797-3XL	3XL	White	10/bg - 3 bgs/cs
PCOAT797-4XL	4XL	White	10/bg - 3 bgs/cs
PCOAT797-5XL	5XL	White	10/bg - 3 bgs/cs

Pharma-Coat® KW **Disposable Lab Coat**

- · Knit wrists and collar
- · Non-shedding
- Spunbond polypropylene
- No Pockets
- ISO Class 7-8



Item #	Size	Color	Selling Unit
PCOAT797-KW-S	S	White	10/bg - 3 bgs/cs
PCOAT797-KW-M	М	White	10/bg - 3 bgs/cs
PCOAT797-KW-L	L	White	10/bg - 3 bgs/cs
PCOAT797-KW-XL	XL	White	10/bg - 3 bgs/cs
PCOAT797-KW-2XL	2XL	White	10/bg - 3 bgs/cs
PCOAT797-KW-3XL	3XL	White	10/bg - 3 bgs/cs
PCOAT797-KW-4XL	4XL	White	10/bg - 3 bgs/cs
PCOAT797-KW-5XL	5XL	White	10/bg - 3 bgs/cs

LEVEL 1

LEVEL 2

5

Pharma-Choice™ **Isolation Gowns**

- · Fluid resistant
- · Disposable, full length; knit cuff
- Latex free
- USP <797> Compliant

- Material: Spunbonded Polypropylene
- Liquid Barrier Test: ANSI / AAMI PB70

- · Material: Polyethlene Coated Spunbonded Polypropylene
- Liquid Barrier Test: ANSI / AAMI PB70
- Water Resistance Impact Penetration Test: AATCC 42
- Water Resistance Hydrostatic Pressure Test: AATCC 127

Item #	Size	Color	Selling Unit
GISO1YL	L	Yellow	10/bg - 5 bgs/cs
GISO1YX	XL	Yellow	10/bg - 5 bgs/cs
GISO1YXX	XXL	Yellow	10/bg - 5 bgs/cs
GISO2BL	L	Blue	10/bg - 5 bgs/cs
GISO2BX	XL	Blue	10/bg - 5 bgs/cs
GISO2BXX	XXL	Blue	10/bg - 5 bgs/cs

Minimum Apparel Recommendations*						
	ISO 8 (Class 100,000)	ISO 7 (Class 10,000)	ISO 6 (Class 1,000)	ISO 5 (Class 100)	ISO 4 (Class 10)	
Hair Cover	•	•	•	•	•	
Beard Cover & Face Cover	•	•	•	•	•	
Hood				•	•	
Booties			•	•	•	
Lab Coat	•	•				
Coverall			•	•	•	
Gloves				•	•	

^{*}These diagrams are a recommendation only. Follow your specific cleanroom or company procedural manual before this guide. The information supplied is for guidance only and should not be construed as a warranty. All implied warranties are expressly disclaimed, including without limitation any warranty of merchantability and fitness for use. All users of the material are responsible for assuring that it is suitable for their needs, environment and end use. All data is subject to change as deemed appropriate.

Controlled Environment Solutions P: 800.942.9199 F: 216.279.0019 hospecobrands.com

Protect 800™ **Sterile Chemo Gloves**

- · Sterile chemo-gloves are your first line of defense against the harmful effects of HD's
- · Ambidextrous, powder free, and made of nitrile
- · Perfect for cancer centers, administration of chemo, handling of HDs, and for compounding chemo
- 12" long for added safety
- Packaged in 100% poly for lint-free donning
- Textured fingertips for extra grip; extended cuffs for added protection
- Tested for a range of chemotherapy drugs



Item#	Size	Finger Thickness	Color	Selling Unit
PROSNCG-S	S	7 mil	Blue	50 pair/bg - 4 bgs/cs
PROSNCG-M	М	7 mil	Blue	50 pair/bg - 4 bgs/cs
PROSNCG-L	L	7 mil	Blue	50 pair/bg - 4 bgs/cs
PROSNCG-XL	XL	7 mil	Blue	50 pair/bg - 4 bgs/cs

Not available for sale in Canada

Pharma-Glove™ Sterile Nitrile Exam Chemo **Rated Gloves**

- · Silicone free
- Not for surgical use
- Validated Sterile
- · Powder Free; Finger Textured
- 100% Nitrile; Latex Free
- 12" Long Extended Cuff
- Tested for use with Chemotherapy Drugs (ASTM-D6978-05 Tested)
- UPS <797> and UPS <800> Compliant
- · Sterilization Method: Gamma Irradiation
- · Min Dose: 25kGy
- · Dose Verification: AAMI Method
- · Pair packaged



Item #	Size	Finger Thick- ness	Color	Selling Unit
PGNS12-XS	XS	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-S	S	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-M	М	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-L	L	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-XL	XL	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-2XL	2XL	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-3XL	3XL	5 mil	White	50 pair/bg - 4 bgs/cs
PGNS12-LTC-XS	XS	5 mil	White	50 pair/bg - 2 bgs/cs
PGNS12-LTC-S	S	5 mil	White	50 pair/bg - 2 bgs/cs
PGNS12-LTC-M	M	5 mil	White	50 pair/bg - 2 bgs/cs
PGNS12-LTC-L	L	5 mil	White	50 pair/bg - 2 bgs/cs
PGNS12-LTC-XL	XL	5 mil	White	50 pair/bg - 2 bgs/cs
PGNS12-LTC-2XL	2XL	5 mil	White	50 pair/bg - 2 bgs/cs
PGNS12-LTC-3XL	3XL	5 mil	White	50 pair/bg - 2 bgs/cs

Not available for sale in Canada

Virtu-Clean™ Class 100 Compatible Powder Free Nitrile Examination Gloves

- Patient examination grade
- · Non sterile
- Powder free; textured fingers
- Ambidextrous
- 100% Nitrile; Latex Free
- 12" long for added safety
- USP <800> Compliant
- ISO Class 5 / Class 100 Compatible
- Tested For Use With Chemotherapy Drugs Per ASTM D6978



Item#	Size	Finger Thickness	Color	Selling Unit
GL-NCREXS	XS	4.5 mil	White	100 gloves/bg - 10 bgs/cs
GL-NCRES	S	4.5 mil	White	100 gloves/bg - 10 bgs/cs
GL-NCREM	М	4.5 mil	White	100 gloves/bg - 10 bgs/cs
GL-NCREL	L	4.5 mil	White	100 gloves/bg - 10 bgs/cs
GL-NCREX	XL	4.5 mil	White	100 gloves/bg - 10 bgs/cs

Not available for sale in Canada

Cleanroom Liquid Cleaners

Virtu-Clean[®] Sterile 70% Isopropyl Alcohol

- Validated sterile
- Available in 16 oz trigger spray bottle
- · Removes many surface contaminants
- Used for wiping down gloved hands, vials, equipment, supplies, counter tops, floors, walls and more
- Double bagged
- ISO class 5
- USP <797> and USP <800> compliant
- Sterile 70% Isopropyl Alcohol (IPA) is listed throughout the USP <797> and <800> requirements as appropriate for a wide variety of processes and procedures



Item #	Size	Sterility	Selling Unit
HBG703016797 ★	16 oz	Validated Sterile	12 bottles /cs

Not available for sale in Canada

Cleanroom Paper

Cleanroom Paper

- Paper Dimensions: 8.5" x 11"
- Brightness%: 88-92
- Used for writing, printing and photocopying in cleanroom environments
- Suitable for use in class 10 to Class 1000 (ISO class 4 to Class 6) cleanroom
- Pure image Premier Paper produced in Class 10 (ISO 4) cleanroom
- · Excellent printability and heat toner adhesion
- · Double sided web cleaned prior to sheeting
- High opacity and durability
- USP <797> Compliant



Item#	Description	Color	Selling Unit
PCIW1082C	22#, Latex Free	White	250 sheets/ream - 10 reams/cs
PCIW1096C	28#, Latex Free	White	250 sheets/ream - 10 reams/cs

Cleanroom Floor Tacky Mats and Frames

Tacky Traxx™ Mats


- Designed to remove particulate from foot and cart traffic upon entering a cleanroom
- Made of high quality incinerable polyethylene film with an adhesive surface featuring just the right amount of "tack"
- · The highly engineered film has a durable and smooth surface that is not easily damaged by heavy foot traffic and cart wheels
- · Each clean film adhesive mat features numbered corner tabs for easy tracking of remaining sheets
- Peel-off sheets eliminate the need for messy cleaning and make it easy to maintain a clean surface; all tacky sheets are numbered in reverse order
- · Can be used for cleanroom and industrial purposes
- Tacky mat frames can be easily lifted to allow cleaning underneath
- Provides a designated area for your cleanroom tacky mats
- · Enables tacky mat to be moved to various areas of the facility
- · Lightweight and durable PVC
- · Non-skid mesh backing

Item #	Description	Color	Size	Layers/ Mat	Selling Unit
Tacky Floor Mat	s				
TT-1836-34B ★	Sticky Floor Mat	Blue	18" x 36"	30	4 mats/cs
TT-1845-34B	Sticky Floor Mat	Blue	18" x 45"	30	4 mats/cs
TT-2436-34B ★	Sticky Floor Mat	Blue	24" x 36"	30	4 mats/cs
TT-3636-34B	Sticky Floor Mat	Blue	36" x 36"	30	4 mats/cs
TT-2445-34B	Sticky Floor Mat	Blue	24" x 45"	30	4 mats/cs
TT-2645-34B	Sticky Floor Mat	Blue	26" x 45"	30	4 mats/cs
TT-3645-34B	Sticky Floor Mat	Blue	36" x 45"	30	4 mats/cs
TT-3660-34B	Sticky Floor Mat	Blue	36" x 60"	30	4 mats/cs
TT-1836-34W	Sticky Floor Mat	White	18" x 36"	30	4 mats/cs
TT-2436-34W	Sticky Floor Mat	White	24" x 36"	30	4 mats/cs
TT-3636-34W	Sticky Floor Mat	White	36" x 36"	30	4 mats/cs
TT-2645-34W	Sticky Floor Mat	White	26" x 45"	30	4 mats/cs
TT-3645-34W	Sticky Floor Mat	White	36" x 45"	30	4 mats/cs
TT-3660-34W	Sticky Floor Mat	White	36" x 60"	30	4 mats/cs
TT-1836-34G	Sticky Floor Mat	Gray	18" x 36"	30	4 mats/cs
TT-1845-34G	Sticky Floor Mat	Gray	18" x 45"	30	4 mats/cs
TT-3636-34G	Sticky Floor Mat	Gray	36" x 36"	30	4 mats/cs
TT-2445-34G	Sticky Floor Mat	Gray	24" x 45"	30	4 mats/cs
TT-2545-34G	Sticky Floor Mat	Gray	25" x 45"	30	4 mats/cs
TT-3645-34G	Sticky Floor Mat	Gray	36" x 45"	30	4 mats/cs
Tacky Mat Frame	es - PVC				
TTF-0-1937	Use with 18" x 36" mats	White	19" x 37"	-	1 each
TTF-0-2537	Use with 24" x 36" mats	White	25" x 37"	-	1 each
TTF-0-2746	Use with 26" x 45" mats	White	27" x 46"	-	1 each
TTF-0-3737	Use with 36" x 36" mats	White	37" x 37"	-	1 each
TTF-0-3761	Use with 36" x 60" mats	White	37" x 61"	-	1 each
High Visibility Ta	acky Mat Frames				
TTF-ALERT	Tacky Traxx [™] Alert! Mat Frame w/ glowing edges and gripper base	Yellow/ Green	24" x 31"	-	1 each
Custom Printed	Tacky Floor Mats and Fra	mes			
TT-2230-38CL *	Clear Sticky Floor Mat	Clear	22.5" x 30"	30	8 mats/cs
TTF-LOGO ★	Custom Printed Frame w/ Gripper Base	White	23.5" x 31"	-	1 each

Sterilization Pouches

Sterilization Pouches

- Designed for use in steam (vapor) and ethylene oxide (ETO) sterilizers
- · Manufactured in an ISO certified facility under strict quality control
- · Feature both built-in internal and external indicators to confirm sterility of the contents, meeting the CDC's recommendation



Item#	Description	Size	Selling Unit
SPH2338	Sterile Pouch	2.25" x 2.75"	200/bx -20 bxs/cs
SPH2350	Sterile Pouch	2.25" x 4"	200/bx -20 bxs/cs
SPH2390	Sterile Pouch	2.25" x 7.75"	200/bx -10 bxs/cs
SPH2810	Sterile Pouch	2.75" x 9"	200/bx -10 bxs/cs
SPH3510	Sterile Pouch	3.5" x 9"	200/bx -10 bxs/cs
SPH3510HY	Sterile Pouch - Economy	3.5" x 9"	200/bx -20 bxs/cs
SPH3565	Sterile Pouch	3.5" x 5.25"	200/bx -10 bxs/cs
SPH5311	Sterile Pouch	5.25" x 10.25"	200/bx -10 bxs/cs
SPH5385	Sterile Pouch	5.25" x 7.5"	200/bx -10 bxs/cs
SPH7514	Sterile Pouch	7.5" x 13"	100/bx -10 bxs/cs
SPH1016	Sterile Pouch	10" x 14.5"	100/bx -10 bxs/cs
SPH1219	Sterile Pouch	12" x 17.75"	100/bx -10 bxs/cs

Cleanroom Absorbent Mat

Cobalt Blue™ Chemo Prep Mats / Spill Pads

- · Ideal for use in your cleanroom, barrier isolator, or glove box during HD compounding
- · These chemo mats will quickly and safely remove spills before they spread
- · Absorbent, 3 ply material
- · Polyethylene and fiber blend
- · Validated Sterile and Non-Sterile Available
- Sterile option is validated to SAL (Sterility Assurance Level) of 10⁻⁶
- · Non-porous polyethylene backing
- · Ideal for ISO class 5 cleanrooms and higher
- · Made in the USA

	Item#	Description	Color	Size	Selling Unit	
	Sterile Chemo I	Mats				
	CBCM-1611.15	Gamma Irradiated, Lint Free, Highly Absorbent, Non-Porous Backing	Blue	16" x 11"	15 mats/bg - 10 bgs/cs	
		Gamma Irradiated, Lint Free, Highly Absorbent, Non-Porous Backing	Blue	22" x 16"	10 mats/bg - 20 bgs/cs	
	Non-Sterile Che	emo Mats				
	CM-1611.50	Non-Sterile, Lint Free, Highly Absorbent, Non-Porous Backing	Blue	16" x 11"	50 mats/bg - 4 bgs/cs	
	CM-2216.50	Non-Sterile, Lint Free, Highly Absorbent, Non-Porous Backing	Blue	22" x 16"	50 mats/bg - 4 bgs/cs	





Innovative SPHERGO SWIVEL® mop handle eases wrist strain. Ease of motion, better reach make life easier for cleaning professionals.

Repetitive stress injuries (RSIs) are a hazard of working as a professional cleaner, but it doesn't have to be this way. The Sphergo® line of ergonomic surface cleaning tools continues to improve working conditions for these vital members of the workforce with the new Sphergo Swivel® mopping tool, specially designed to reduce RSIs.

SPHERGO SWIVEL® Mopping Tool

- The Sphergo Swivel® unique curved pole positions the user's body posture optimally to reduce repetitive strain injuries
- The rotating ball handle reduces unnecessary wrist motion while improving grip and control
- The curved pole paired with rotating ball on the handle allows for effortless smooth mopping "S" motion
- Sphergo Swivel® curved pole allows for farther reach underneath low-clearance obstructions like beds, chairs, and desks relative to a tradition straight mop while eliminating awkward bending
- Trapezoid frame design provides easier access into corners and along baseboards while making pad removal effortless
- The base's rounded edges help prevent any damage to sensitive areas such as wood trim or wooden furniture legs
- Replaceable hook and loop strips
- · Lightweight aluminum frame



Rotating ball handle allows for improved grip and control.




Curved pole allows for farther reach under beds, chairs and more.



Trapezoid frame design provides easier access into corners.

Item#	Description	Selling Unit	Case Pack
2505-SWPOLE	Sphergo Swivel® White Aluminum Extension Pole	1 ea	12/cs
2505-SWBASE	Sphergo Swivel® White Aluminum Base for 18"-20" Pads	1 ea	12/cs
SPH-SWKT	Sphergo Swivel® Starter Kit Tools: (1) White Aluminum Extension Pole, (1) White Aluminum Base, Pads*: (12) Virtu-Clean® VCU2 pads, (12) Virtu-Clean® VCDCS pads	1 kit	1 kit/cs



^{*}During the transition period you may receive a kit that contains (12) Virtu-Clean® VCU pads, (12) Virtu-Clean® VCDC pads, (12) Virtu-Clean® VCDC pads

The Sphergo Swivel® pole and base combination can be used with any 18"-20" disposable or reusable microfiber flat pad, but we recommend pairing Sphergo Swivel® with the Virtu-Clean® line of disposable cleaning pads for even more efficacious cleaning and less worker strain! These specially engineered pads are designed to reduce friction while maximizing cleaning results and coverage area.



Charge once, even coverage, and a cleaner floor.

Not all cleaning pads are equal. Absorbency rates, release rates, coverage, and linting can vary greatly, significantly impacting the finished product. Virtu-Clean® Disposable Cleaning Pads are specially engineered for critical environments, giving you maximum coverage, cleaning, and convenience. Our disposable, single-use mop pads check all the right boxes – they hold more liquid, release that liquid at a controlled rate over a larger surface area, and reduce friction for more effort-free cleaning.

Virtu-Clean® Disposable Cleaning Pads

VCU2 | Virtu-Clean® Universal Disposable Cleaning Pad

- VCU2 offers the same efficacy as the original VCU, but now includes up to 90% recycled content!
- USP <797> Compliant for pharmacy sterile compounding and sterile preparations
- Eco friendly manufacturing with no chemical dyes used in the process
- · Contains up to 90% post-consumer recycled content
- Single use application to reduce risk of cross contamination
- No quat binding
- Compatible with chlorine bleach, hydrogen peroxide, and common disinfectants up to 400 sq. ft. cleaning coverage
- · Absorbs 9x its weight in liquid
- Superior absorbency and release provides consistent coverage and cleaning
- Embossed pattern reduces friction for less strain on workers
- · Channels efficiently pick up and retain dirt in pad
- Bonded edges improve performance greatly, reducing linting for a cleaner clean
- Polyester backing produces less lint upon removal from base
- Bag in bag packaging for cleanroom application
- Perfect for foodservice and food processing operations, healthcare facilities, cleanrooms, controlled environments, surgical rooms, ICU areas, pharmacy applications, and other institutions

VCDCS | Virtu-Clean® DCS Disposable Cleaning Pad w/Scrubber

Similar to the VCU2 pad, but with built in scrubbers for more aggressive cleaning and stain removal. With up to 48% recycled content, our VCDCS pads holds nearly 6x their weight in cleaning fluid, which translates into 240-300 sq. ft. of cleaning coverage with a single charge.







Cleaning pads marked with this symbol are environmentally friendly with 48% - 90% post-consumer recycled content.

9

All pad options can be used with most flat mop bases; however, Hospeco Brands Group designed and recommends the pads be used with the new Sphergo Swivel®, for a more complete ergonomic cleaning solution.

Item#	Description	ISO Class	Size	Selling Unit
VCU2 P	Virtu-Clean® Universal Disposable Cleaning Pad	ISO Class 5	5" x 19"	20 pads/bg, 12 bgs/master bg - 1 master bg/cs
VCDCS P	Virtu-Clean® DCS Disposable Cleaning Pad w/Scrubber	ISO Class 5	5" x 19"	20 pads/bg, 12 bgs/master bg - 1 master bg/cs
SPH-SWKT	Sphergo Swivel® Starter Kit Tools: (1) White Aluminum Extension Pole, (1) White Aluminum Base, Pads*: (12) Virtu-Clean® VCU2 pads, (12) Virtu-Clean® VCDCS pads	-	-	1 kit

^{*}During the transition period you may receive a kit that contains (12) Virtu-Clean® VCU pads, (12) Virtu-Clean® VCDC pads, (12) Virtu-Clean® VCDCS pads

P: 800.942.9199 F: 216.279.0019 hospecobrands.com **Controlled Environment Solutions**

Product Weight and Pallet Quantity Information

Dry Wipes: Non-Sterile NT1-44 1 cs 24 20 NT1-9912 1 cs 32 30 NT1-1212 1 cs 34 36 VS20-99 1 cs 22 50 VS20-1212 1 cs 33 30 ULT70-99 1 cs 38 50 Dry Wipes: Sterile NT1-1212CB 1 cs 32 64 NT1-1212CB 1 cs 33 54 GR-NT1-99 1 cs 28 32 GE-NT1-99 1 cs 28 32 GE-DISP-SS 1 ea 11 27 Presaturated Wipes: Non-Sterile FS-NT1-69-9C 1 cs 38 27 FS-NT1-991 1 cs 25 30 FS-NT1-911.85 1 cs 50 30 FS-NT1-7911.85 1 cs 26 40 FS-NT-1911.85 1 cs 26 40 FS-NT-171.85 1 cs	Item#	Selling Unit	UOS Wt.	UOS PLT
NTI-99.12 1cs 32 30 NTI-1212 1cs 34 36 VS20-99 1cs 22 50 VS20-1212 1cs 33 30 ULT70-99 1cs 38 50 Dry Wipes: Sterile NTI-99CB 1cs 32 64 NTI-1212CB 1cs 33 54 GRAB-EEZ™ Dry Wipes & Dispenser GE-NTI-99 1cs 28 32 64 GRAB-EEZ™ Dry Wipes & Dispenser GE-NTI-99 1cs 28 32 65 CE-DISP-SS 1ca 11 27 Presaturated Wipes: Non-Sterile FS-NTI-77 1cs 24 40 FS-NTI-69-9C 1cs 38 27 FS-NTI-99 1cs 28 40 FS-NTI-99 1cs 28 40 FS-NTP-911 1cs 25 30 SS-NTI-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-911 1cs 25 30 FS-NTP-911 1cs 25 30 SS-NTI-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1cs 50 30 SS-NTI-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1cs 56 40 GAH-BP-21-WH 1cs 6 84 GAH-BP-21-WH 1cs 7 84 GAH-BP-24-WH 1cs 7 84 GAH-BP-24-WH 1cs 7 84 GAH-BP-24-WH 1cs 7 84 GAH-BP-24-WH 1cs 7 84 GAH-BP-28-WH 1cs 9 54 GAH-BP-28-WH 1cs 9 54 GAH-BP-28-WH 1cs 7 42 GAH-BP-28-WH 1cs 7 42 GAH-BP-28-WH 1cs 7 42 GAH-BP-28-WH 1cs 7 42 GAH-BP-18-BL 1cs 7 42 GAH-BP-18-BL 1cs 7 42 GAH-BP-18-BL 1cs 7 42 GAH-BP-NS-LG 1cs 5 108 GAH-SP-NS-LG 1cs 5 108	Dry Wipes: Non-Sterile			
NTI-1212 1cs 34 36 VS20-99 1cs 22 50 VS20-1212 1cs 33 30 ULT70-99 1cs 38 50 Dry Wipes: Sterile NTI-99CB 1cs 32 64 NTI-1212CB 1cs 33 54 GRAB-EEZTM Dry Wipes & Dispenser GE-NTI-99 1cs 28 32 GE-DISP-SS 1ea 11 27 Presaturated Wipes: Non-Sterile FS-NTI-77 1cs 24 40 FS-NTI-69-9C 1cs 38 27 FS-NTI-99 1cs 28 40 FS-NTI-991 1cs 28 40 FS-NTP-911 1cs 25 30 SS-NTI-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-911 1cs 25 40 FS-NTP-911 1cs 50 30 SS-NTI-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-911-35CB 1cs 50 30 SS-NTI-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-91-12.35CB Bee-Safe® Bouffant Caps GAH-BP-24-WH 1cs 6 84 GAH-BP-24-WH 1cs 7 84 GAH-BP-28-WH 1cs 9 54 GAH-BP-28-WH 1cs 9 54 GAH-BP-28-BL 1cs 9 54 Bee-Safe® Beard Covers GAH-BP-0D-WH 1cs 7 42 GAH-BP-0D-WH 1cs 7 42 GAH-BP-NS-LG 1cs 5 108 GAH-SP-NS-LG 1cs 5 108 GAH-SP-NS-LG 5 108 GAH-SP-NS-LG 5 108 GAH-SP-NS-LG 1cs 5 108	NT1-44	1cs	24	20
VS20-99	NT1-99.12	1cs	32	30
VS20-1212	NT1-1212	1cs	34	36
Dry Wipes: Sterile	VS20-99	1cs	22	50
NT1-99CB 1 cs 32 64 NT1-1212CB 1 cs 33 54 GRAB-EEZ™ Dry Wipes & Dispenser GE-NT1-99 1 cs 28 32 GE-DISP-SS 1 ea 11 27 Presaturated Wipes: Non-Sterile FS-NT1-77 1 cs 24 40 FS-NT1-69-9C 1 cs 38 27 FS-NTP-911 1 cs 25 30 FS-NTP-911.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NTP-911.35CB 1 cs 26 40 FS-NTP-911.35CB 1 cs 26 40 FS-NTP-911.35CB 1 cs 3 40 FS-NTP-911.35CB 1 cs 4 4 Bee-Safe® Bouffant Caps 4 4 4 4 4 4 4 4 4 4 4	VS20-1212	1cs	33	30
NT1-99CB 1 cs 32 64 NT1-1212CB 1 cs 33 54 GRAB-EEZ™ Dry Wipes & Dispenser GE-NT1-99 1 cs 28 32 GE-DISP-SS 1 ea 11 27 Presaturated Wipes: Non-Sterile FS-NT1-77 1 cs 24 40 FS-NT1-99 1 cs 28 40 FS-NTP-911 1 cs 25 30 FS-NTP-911.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB 1 cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-WH 1 cs 7 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 B	ULT70-99	1cs	38	50
NTI-1212CB 1 cs 33 54 GRAB-EEZ™ Dry Wipes & Dispenser GE-NT1-99 1 cs 28 32 GE-DISP-SS 1 ea 11 27 Presaturated Wipes: Non-Sterile FS-NT1-77 1 cs 24 40 FS-NT1-99 1 cs 28 40 FS-NTP-911 1 cs 25 30 FS-NTP-1711.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB 1 cs 26 40 FS-NT1-912.35CB 1 cs 26 40 Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-22-WH 1 cs 7 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 Bee-Safe® Beard Covers 84 135 Bee-Safe® Polypropylene Hoods	Dry Wipes: Sterile			
GRAB-EEZ™ Dry Wipes & Dispenser GE-NT1-99 1 cs 28 32 GE-DISP-SS 1 ea 11 27 Presaturated Wipes: Non-Sterile FS-NT1-77 1 cs 24 40 FS-NT1-69-9C 1 cs 38 27 FS-NT1-99 1 cs 28 40 FS-NTP-911 1 cs 25 30 FS-NTP-911 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NTP-911.35CB 1 cs 26 40 FS-NTP-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-H00D-WH 1 cs 7 42 GAH-H00D-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108	NT1-99CB	1cs	32	64
GE-NTI-99 1 cs 28 32 GE-DISP-SS 1 ea 11 27 Presaturated Wipes: Non-Sterile FS-NT1-77 1 cs 24 40 FS-NT1-69-9C 1 cs 38 27 FS-NT1-99 1 cs 28 40 FS-NT1-991 1 cs 25 30 FS-NTP-1711.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB 1 cs 26 40 Presaturated Wipes: Sterile FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-WH 1 cs 7 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BP-28-BL	NT1-1212CB	1cs	33	54
Presaturated Wipes: Non-Sterile FS-NT1-77	GRAB-EEZ™ Dry Wipes & Dispense	er		
Presaturated Wipes: Non-Sterile FS-NT1-77 1 cs 24 40 FS-NT1-69-9C 1 cs 38 27 FS-NT1-99 1 cs 28 40 FS-NTP-911 1 cs 25 30 FS-NTP-1711.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB 1 cs 26 40 FS-NTP-911.35CB 1 cs 6 84 GAH-BP-911.35CB 1 cs 6 84 GAH-BP-21.35CB 1 cs 7 84 GAH-BP-21.BL 1 cs 7 42 GAH-BP-28-WH 1 cs 7 42	GE-NT1-99	1cs	28	32
FS-NT1-77	GE-DISP-SS	1 ea	11	27
FS-NT1-69-9C 1 cs 38 27 FS-NT1-99 1 cs 28 40 FS-NTP-911 1 cs 25 30 FS-NTP-1711.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-24-BL 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 9 54 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108	Presaturated Wipes: Non-Sterile			
FS-NTI-99 1 1 cs 28 40 FS-NTP-911 1 cs 25 30 FS-NTP-1711.85 1 cs 50 30 SS-NTI-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NTI-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 7 42 GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108	FS-NT1-77	1cs	24	40
FS-NTP-911 1 cs 25 30 FS-NTP-1711.85 1 cs 50 30 SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 GAH-BP-28-BL 1 cs 7 42 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	FS-NT1-69-9C	1cs	38	27
FS-NTP-1711.85 1cs 50 30 SS-NT1-77 1cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1cs 6 84 GAH-BP-24-WH 1cs 7 84 GAH-BP-24-BL 1cs 7 84 GAH-BP-28-BL 1cs 9 54 GAH-BP-28-BL 1cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1cs 7 42 GAH-HOOD-BL 1cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1cs 5 108 GAH-SP-NS-ZXL 1cs 5 108 GAH-SC-S-LG 1cs 7 72	FS-NT1-99	1cs	28	40
SS-NT1-77 1 cs 9 40 Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 Bee-Safe® Beard Covers GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Polypropylene Hoods GAH-BRD-WH 1 cs 7 42 Bee-Safe® Shoe Covers GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	FS-NTP-911	1cs	25	30
Presaturated Wipes: Sterile FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 7 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108 GAH-SC-S-LG 1 cs 5 108	FS-NTP-1711.85	1cs	50	30
FS-NTP-911.35CB 1 cs 26 40 FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	SS-NT1-77	1cs	9	40
FS-NT1-912.35CB Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 Bee-Safe® Beard Covers 9 54 Bee-Safe® Polypropylene Hoods 1 cs 4 135 Bee-Safe® Polypropylene Hoods 1 cs 7 42 Bee-Safe® Shoe Covers 2 4 1 cs 5 108 GAH-SP-NS-LG 1 cs 5 108 5 108 5 108 GAH-SP-NS-XL 1 cs 5 108 5 108 5 108 5 108 5 108 5 108 5 108 5 108 5 108 5 108 5 108 5 108 5 108 6 108 6 6 <td>Presaturated Wipes: Sterile</td> <td></td> <td></td> <td></td>	Presaturated Wipes: Sterile			
Bee-Safe® Bouffant Caps GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 9 54 GAH-BP-28-WH 1 cs 9 54 Bee-Safe® Beard Covers 8 9 54 Bee-Safe® Polypropylene Hoods 1 cs 4 135 Bee-Safe® Polypropylene Hoods 1 cs 7 42 GAH-HOOD-WH 1 cs 7 42 Bee-Safe® Shoe Covers 1 cs 5 108 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 7 72	FS-NTP-911.35CB	1cs	26	40
GAH-BP-21-WH 1 cs 6 84 GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-ZXL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	FS-NT1-912.35CB			
GAH-BP-21-BL 1 cs 6 84 GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 7 7	Bee-Safe® Bouffant Caps			
GAH-BP-24-WH 1 cs 7 84 GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BP-21-WH	1cs	6	84
GAH-BP-24-BL 1 cs 7 84 GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BP-21-BL	1cs	6	84
GAH-BP-28-WH 1 cs 9 54 GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BP-24-WH	1cs	7	84
GAH-BP-28-BL 1 cs 9 54 Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods Sah-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BP-24-BL	1cs	7	84
Bee-Safe® Beard Covers GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BP-28-WH	1cs	9	54
GAH-BRD-WH 1 cs 4 135 Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BP-28-BL	1cs	9	54
Bee-Safe® Polypropylene Hoods GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	Bee-Safe® Beard Covers			
GAH-HOOD-WH 1 cs 7 42 GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-BRD-WH	1cs	4	135
GAH-HOOD-BL 1 cs 7 42 Bee-Safe® Shoe Covers 5 108 GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	Bee-Safe® Polypropylene Hoods			
Bee-Safe® Shoe Covers GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-HOOD-WH	1cs	7	42
GAH-SP-NS-LG 1 cs 5 108 GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-HOOD-BL	1cs	7	42
GAH-SP-NS-XL 1 cs 5 108 GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	Bee-Safe® Shoe Covers			
GAH-SP-NS-2XL 1 cs 5 108 GAH-SC-S-LG 1 cs 7 72	GAH-SP-NS-LG	1cs	5	108
GAH-SC-S-LG 1cs 7 72	GAH-SP-NS-XL	1cs	5	108
	GAH-SP-NS-2XL	1cs	5	108
GAH-SC-S-XL 1 cs 10 54	GAH-SC-S-LG	1cs	7	72
	GAH-SC-S-XL	1cs	10	54

Item#	Selling Unit	UOS Wt.	UOS PLT
Pharma-Coat® Disposable Lab Coats			
PCOAT797-S	1 cs	7	60
PCOAT797-M	1cs	7	60
PCOAT797-L	1 cs	7	60
PCOAT797-XL	1cs	7	60
PCOAT797-2XL	1cs	7	60
PCOAT797-3XL	1cs	7	60
PCOAT797-4XL	1cs	7	60
PCOAT797-5XL	1cs	7	60
Pharma-Coat® KW Disposable Lab Coats			
PCOAT797-KW-S	1cs	8	60
PCOAT797-KW-M	1cs	8	60
PCOAT797-KW-L	1cs	8	60
PCOAT797-KW-XL	1cs	8	60
PCOAT797-KW-2XL	1cs	8	60
PCOAT797-KW-3XL	1cs	8	60
PCOAT797-KW-4XL	1cs	8	60
PCOAT797-KW-5XL	1cs	8	60
Pharma-Choice Isolation Gowns			
GISO1YL	1cs	11	63
GISO1YX	1cs	11.5	63
GISO1YXX	1cs	13.5	63
GISO2BL	1cs	11	63
GISO2BX	1cs	11.5	63
GISO2BXX	1cs	13.5	63
Pharma-Glove™ Sterile Nitrile Exam Cher	no Rated Gloves		
PGNS12-XS	1cs	15	72
PGNS12-S	1cs	15	72
PGNS12-M	1cs	15	72
PGNS12-L	1cs	15	72
PGNS12-XL	1cs	16	72
PGNS12-2XL	1cs	16	72
PGNS12-3XL	1cs	16	72
PGNS12-LTC-XS	1cs	16	84
PGNS12-LTC-S	1cs	16	84
PGNS12-LTC-M	1cs	16	84
PGNS12-LTC-L	1cs	16	84
PGNS12-LTC-XL	1cs	16	84
PGNS12-LTC-2XL	1cs	16	84
PGNS12-LTC-3XL	1cs	16	84

Protect 800™ Sterile Chemo Gloves PROSNCG-S	Item#	Selling Unit	UOS Wt.	UOS PLT	
PROSNCG-M PROSNCG-L 1 cs 15 72 PROSNCG-L 1 cs 15 72 PROSNCG-L 1 cs 15 72 PROSNCG-XL 1 cs 15 72 PROSNCG-XL 1 cs 15 72 Virtu-Clean™ Cleanroom Gloves GL-NCRES 1 cs 15 72 GL-NCREM 1 cs 16 72 GL-NCREL 1 cs 16.5 72 GL-NCREX 1 cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1082C 1 cs 25 TBD PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-2436-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 19 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 19 60 TT-3660-34B 1 cs 19 60 TT-3660-34W 1 cs 7 60 TT-2436-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 11 60 TT-3636-34W 1 cs 13 60 TT-3636-34W 1 cs 14 60 TT-3636-34W 1 cs 18 60 TT-3636-34W 1 cs 19 60 TT-3636-34G 1 cs 14 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60	Protect 800™ Sterile Chemo Gloves				
PROSNCG-L PROSNCG-XL 1 cs 15 72 PROSNCG-XL 1 cs 15 72 Virtu-Clean™ Cleanroom Gloves GL-NCRES 1 cs 15.5 72 GL-NCRES 1 cs 15.5 72 GL-NCREM 1 cs 16.5 72 GL-NCREL 1 cs 16.5 72 GL-NCREX 1 cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1082C 1 cs 25 TBD PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-2445-34B 1 cs 11 60 TT-2445-34B 1 cs 11 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3636-34B 1 cs 13 60 TT-3636-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-2436-34B 1 cs 13 60 TT-2645-34B 1 cs 13 60 TT-2645-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 19 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34W 1 cs 10 60 TT-3636-34W 1 cs 13 60 TT-3636-34W 1 cs 14 60 TT-3636-34G 1 cs 9 60 TT-1836-34G 1 cs 9 60 TT-1845-34G 1 cs 14 60 TT-2445-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60	PROSNCG-S	1cs	15	72	
PROSNCG-XL 1 cs 15 72 Virtu-Clean™ Cleanroom Gloves GL-NCREXS 1 cs 15.5 72 GL-NCRES 1 cs 16.5 72 GL-NCREM 1 cs 16.5 72 GL-NCREX 1 cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1082C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-2436-34B 1 cs 9 60 TT-1845-34B 1 cs 10 60 TT-2436-34B 1 cs 10 60 TT-2436-34B 1 cs 14 60 TT-2436-34B 1 cs 13 60 TT-2436-34B 1 cs 13 60 TT-2645-34B 1 cs 13 60	PROSNCG-M	1cs	15	72	
Virtu-Clean™ Cleanroom Gloves GL-NCREXS 1 cs 15 72 GL-NCRES 1 cs 15.5 72 GL-NCREM 1 cs 16.5 72 GL-NCREL 1 cs 16.5 72 GL-NCREX 1 cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-2436-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-2445-34B 1 cs 11 60 TT-2445-34B 1 cs 13 60 TT-3636-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 <td colsp<="" td=""><td>PROSNCG-L</td><td>1cs</td><td>15</td><td>72</td></td>	<td>PROSNCG-L</td> <td>1cs</td> <td>15</td> <td>72</td>	PROSNCG-L	1cs	15	72
GL-NCRESS 1cs 15.5 72 GL-NCREM 1cs 16.5 72 GL-NCREL 1cs 16.5 72 GL-NCREL 1cs 16.5 72 GL-NCREX 1cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1cs 11 64 Cleanroom Paper PCIW1098C 1cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1cs 7 60 TT-2436-34B 1cs 10 60 TT-2436-34B 1cs 11 60 TT-2445-34B 1cs 11 60 TT-245-34B 1cs 11 60 TT-245-34B 1cs 11 60 TT-245-34B 1cs 11 60 TT-3636-34B 1cs 11 60 TT-245-34B 1cs 11 60 TT-245-34B 1cs 11 60 TT-3636-34B 1cs 13 60 TT-3645-34B 1cs 13 60 TT-3645-34B 1cs 13 60 TT-3645-34B 1cs 18 60 TT-3660-34B 1cs 18 60 TT-3660-34B 1cs 17 60 TT-3660-34B 1cs 18 60 TT-3660-34B 1cs 19 60 TT-3660-34W 1cs 19 60 TT-3660-34G 1cs 11 60 TT-3660-34G 1cs 11 60 TT-3660-34G 1cs 11 60 TT-3645-34G 1cs 11 60 TT-2645-34G 1cs 11 60	PROSNCG-XL	1cs	15	72	
GL-NCREM GL-NCREM GL-NCREM GL-NCREL GL-NCREX GL-NCREX 1cs 16.5 72 GL-NCREX 1cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1cs 11 64 Cleanroom Paper PCIW1082C 1cs 25 TBD PCIW1096C 1cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1cs 7 60 TT-2436-34B 1cs 10 60 TT-3636-34B 1cs 11 60 TT-2455-34B 1cs 11 60 TT-3636-34B 1cs 11 60 TT-2456-34B 1cs 11 60 TT-2456-34B 1cs 11 60 TT-2456-34B 1cs 13 60 TT-245-34B 1cs 16 TT-3636-34B 1cs 16 TT-3636-34B 1cs 16 TT-3636-34B 1cs 16 TT-3645-34B 1cs 16 TT-3645-34B 1cs 17 60 TT-3645-34B 1cs 18 60 TT-3660-34B 1cs 16 TT-3660-34B 1cs 17 60 TT-3636-34B 1cs 17 60 TT-3636-34B 1cs 17 60 TT-3636-34B 1cs 17 60 TT-3636-34B 1cs 16 TT-3636-34B 1cs 17 60 TT-3636-34B 1cs 17 60 TT-3636-34B 1cs 18 60 TT-3636-34B 1cs 19 60 TT-3636-34B 1 cs 11 60 TT-3636-34B 1 cs 11 60 TT-3636-34B 1 cs 12 60 TT-3636-34B 1 cs 11 60 TT-2645-34B 1 cs 11 6 0 TT-2645-34B 1 cs	Virtu-Clean™ Cleanroom Gloves				
GL-NCREM 1 cs 16 72 GL-NCREX 1 cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW10982C 1 cs 25 TBD PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-2436-34B 1 cs 10 60 TT-2445-34B 1 cs 11 60 TT-3636-34B 1 cs 11 60 TT-3636-34B 1 cs 14 60 TT-3636-34B 1 cs 13 60 TT-3645-34B 1 cs 14 60 TT-3645-34B 1 cs 13 60 TT-3660-34B 1 cs 15 16 TT-3660-34B 1 cs 17 60 TT-3636-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-3636-34W 1 cs 15 16 TT-3645-34W 1 cs 17 60 TT-3645-34W 1 cs 11 60 TT-2645-34G 1 cs 11 60	GL-NCREXS	1cs	15	72	
GL-NCREX 1 cs 16.5 72 GL-NCREX 1 cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1082C 1 cs 25 TBD PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-2436-34B 1 cs 10 60 TT-2436-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-3636-34B 1 cs 11 60 TT-245-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 7 60 TT-3636-34W 1 cs 10 60 TT-3636-34W 1 cs 10 60 TT-3636-34W 1 cs 10 60 TT-3636-34W 1 cs 13 60 TT-3636-34W 1 cs 14 60 TT-3636-34W 1 cs 15 16 60 TT-3636-34W 1 cs 17 60 TT-3636-34W 1 cs 18 60 TT-3645-34W 1 cs 19 60 TT-3636-34W 1 cs 19 60 TT-3636-34W 1 cs 19 60 TT-3636-34G 1 cs 14 60 TT-3636-34G 1 cs 14 60 TT-2645-34G 1 cs 11 60	GL-NCRES	1cs	15.5	72	
GI-NCREX 1cs 17 72 Virtu-Clean® Sterile IPA HBG703016797 1cs 11 64 Cleanroom Paper PCIW1082C 1cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1cs 7 60 TT-2436-34B 1cs 10 60 TT-2436-34B 1cs 11 60 TT-2445-34B 1cs 11 60 TT-3636-34B 1cs 11 60 TT-3636-34B 1cs 11 60 TT-3645-34B 1cs 11 60 TT-2445-34B 1cs 11 60 TT-245-34B 1cs 11 60 TT-3636-34B 1cs 13 60 TT-3645-34B 1cs 13 60 TT-3645-34B 1cs 13 60 TT-3645-34B 1cs 13 60 TT-3660-34B 1cs 13 60 TT-3660-34B 1cs 15 16 60 TT-3660-34B 1cs 7 60 TT-3636-34W 1cs 10 60 TT-3636-34W 1cs 10 60 TT-3636-34W 1cs 10 60 TT-3636-34W 1cs 14 60 TT-3636-34W 1cs 15 16 60 TT-3645-34W 1cs 17 60 TT-3645-34W 1cs 17 60 TT-3645-34W 1cs 18 60 TT-3645-34W 1cs 19 60 TT-3645-34W 1cs 19 60 TT-3645-34W 1cs 19 60 TT-3645-34W 1cs 11 60 TT-3645-34G 1cs 14 60 TT-3636-34G 1cs 14 60 TT-2645-34G 1cs 11 60	GL-NCREM	1cs	16	72	
Virtu-Clean® Sterile IPA HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1082C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-2645-34W 1 cs 14 60 TT-2645-34W 1 cs 13 60 TT-3636-34W 1 cs 18 60 TT-3645-34W 1 cs 18 60 TT-3636-34G 1 cs 7 60 TT-3636-34G 1 cs 9 60 <td>GL-NCREL</td> <td>1cs</td> <td>16.5</td> <td>72</td>	GL-NCREL	1cs	16.5	72	
HBG703016797 1 cs 11 64 Cleanroom Paper PCIW1082C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-3636-34W 1 cs 7 60 TT-2436-34W 1 cs 14 60 TT-3645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3636-34G 1 cs 7 60 TT-3636-34G 1 cs 9 60 TT-1845-34G <td>GL-NCREX</td> <td>1cs</td> <td>17</td> <td>72</td>	GL-NCREX	1cs	17	72	
Cleanroom Paper PCIW1082C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-3645-34B 1 cs 13 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 10 60 TT-3636-34W 1 cs 10 60 TT-2436-34W 1 cs 14 60 TT-3645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3645-34W 1 cs 18 60 TT-1845-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2445-34G 1 cs <t< td=""><td>Virtu-Clean® Sterile IPA</td><td></td><td></td><td></td></t<>	Virtu-Clean® Sterile IPA				
PCIW1096C 1 cs 25 TBD PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 11 60 TT-3636-34B 1 cs 11 60 TT-2445-34B 1 cs 11 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 13 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 7 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-2436-34W 1 cs 14 60 TT-3636-34W 1 cs 15 60 TT-3636-34W 1 cs 17 60 TT-3636-34W 1 cs 19 60 TT-3636-34W 1 cs 19 60 TT-3636-34W 1 cs 11 60 TT-3636-34W 1 cs 11 60 TT-3645-34W 1 cs 11 60 TT-3645-34W 1 cs 11 60 TT-3645-34W 1 cs 11 60 TT-3645-34G 1 cs 11 60 TT-2445-34G 1 cs 11 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 11 60	HBG703016797	1cs	11	64	
PCIW1096C 1 cs 25 TBD Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3665-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 14 60 TT-3645-34W 1 cs 13 60 TT-3645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 7 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 7 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 14 60	Cleanroom Paper				
Tacky Traxx™ Mats TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 7 60 TT-1836-34W 1 cs 10 60 TT-2436-34W 1 cs 14 60 TT-3636-34W 1 cs 13 60 TT-3645-34W 1 cs 13 60 TT-3660-34W 1 cs 18 60 TT-3660-34W 1 cs 18 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 7 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	PCIW1082C	1cs	25	TBD	
TT-1836-34B 1 cs 7 60 TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 11 60 TT-3645-34B 1 cs 13 60 TT-3660-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-2645-34W 1 cs 14 60 TT-3636-34W 1 cs 15 60 TT-3636-34W 1 cs 16 60 TT-3636-34W 1 cs 17 60 TT-3636-34W 1 cs 18 60 TT-3636-34W 1 cs 19 60 TT-3636-34G 1 cs 14 60 TT-1836-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60	PCIW1096C	1cs	25	TBD	
TT-1845-34B 1 cs 9 60 TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 13 60 TT-3660-34W 1 cs 18 60 TT-3660-34W 1 cs 18 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	Tacky Traxx™ Mats				
TT-2436-34B 1 cs 10 60 TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-1836-34B	1cs	7	60	
TT-3636-34B 1 cs 14 60 TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 13 60 TT-2645-34W 1 cs 13 60 TT-3660-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-1845-34B	1cs	9	60	
TT-2445-34B 1 cs 11 60 TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 18 60 TT-3660-34W 1 cs 18 60 TT-3660-34W 1 cs 7 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-2436-34B	1cs	10	60	
TT-2645-34B 1 cs 13 60 TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-3636-34B	1cs	14	60	
TT-3645-34B 1 cs 18 60 TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 18 60 TT-3660-34W 1 cs 18 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-2445-34B	1cs	11	60	
TT-3660-34B 1 cs 25 60 TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-2645-34B	1cs	13	60	
TT-1836-34W 1 cs 7 60 TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 13 60 TT-36645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-2445-34G 1 cs 14 60 TT-2545-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-3645-34B	1cs	18	60	
TT-2436-34W 1 cs 10 60 TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-3660-34B	1cs	25	60	
TT-3636-34W 1 cs 14 60 TT-2645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-1836-34W	1cs	7	60	
TT-2645-34W 1 cs 13 60 TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-2436-34W	1cs	10	60	
TT-3645-34W 1 cs 18 60 TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-3636-34W	1cs	14	60	
TT-3660-34W 1 cs 25 60 TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-2645-34W	1cs	13	60	
TT-1836-34G 1 cs 7 60 TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-3645-34W	1cs	18	60	
TT-1845-34G 1 cs 9 60 TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-3660-34W	1cs	25	60	
TT-3636-34G 1 cs 14 60 TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-1836-34G	1cs	7	60	
TT-2445-34G 1 cs 11 60 TT-2545-34G 1 cs 12 60	TT-1845-34G	1cs	9	60	
TT-2545-34G 1 cs 12 60	TT-3636-34G	1cs	14	60	
	TT-2445-34G	1cs	11	60	
TT-3645-34G 1 cs 18 60	TT-2545-34G	1cs	12	60	
	TT-3645-34G	1cs	18	60	

Item#	Selling Unit	UOS Wt.	UOS PLT
Tacky Mat Frames - PVC	Ocining Onit		
TTF-0-1937	 1 ea	3	50
TTF-0-2537	1 ea	4	50
TTF-0-2746	1 ea	4.75	50
TTF-0-3737	1 ea	4.5	50
TTF-0-3761	1ea	5.5	50
High Visibility Tacky Mat Frame			
TTF-ALERT	1ea	3	40
Custom Printed Tacky Mats & Frames			
TT-2230-38CL	1 cs	9.5	40
TTF-LOGO	1ea	3	40
Sterilization Pouches			
SPH2338	1 cs	7.7	144
SPH2350	1cs	9.6	150
SPH2390	1cs	7.6	144
SPH2810	1cs	10.15	147
SPH3510	1cs	13.1	126
SPH3510HY	1cs	25.17	54
SPH3565	1cs	8.6	144
SPH5311	1cs	22.25	60
SPH5385	1cs	16.6	84
SPH7514	1cs	19.1	TBD
SPH1016	1cs	28.35	TBD
SPH1219	1cs	40.35	TBD
Cobalt Blue Chemo Mats			
CBCM-1611.15	1cs	9	48
CBCM-2216.10	1cs	18	32
CM-1611.50	1cs	9	48
CM-2216.50	1cs	18	32
Sphergo Swivel® Mopping Tool			
2505-SWPOLE	1 ea	1.5	396
2505-SWBASE	1 ea	0.8	864
SPH-SWKT	1 kit	3.97	104
Virtu-Clean® Disposable Cleaning Pads			
VCU2	1cs	11.46	32
VCDCS	1cs	11.46	32
SPH-SWKT	1 kit	3.97	104

P: 800.942.9199 F: 216.279.0019 hospecobrands.com Controlled Environment Solutions

DISTRIBUTED BY:



ST. 1916

INDSUPPLY.COM 800-288-3838





Wiping Solutions · Gloves · Cleaning Chemicals · Textiles & Linens · Personal Care · Odor Control Controlled Environments · Safety · Cleaning Tools & Accessories · Food Service · Specialty Products